

HYGIENIC, DISPOSABLE BIB HOLDERS

For a disposable bib holder that doesn't require sterilisation, turn to DUX Dental and Bib-Eze.

Research has proven that bib clips can harbour pathogens and can be a source of cross-contamination – with one in five bib clips showing significant microorganism growth, including that of the *E. coli* pathogen. It therefore makes sense for clinicians to use hygienic, disposable bib holders such as Bib-Eze from DUX.


The cost-effective Bib-Eze can be used in conjunction with any paper bib. Hygienic and comfortable, the product is made from soft, elasticised fibre and features self-adhesive tips that attach to the patient's bib – so

patients no longer have to flinch as cold bib chains touch their skin.

By using Bib-Eze, clinicians not only increase standards of infection control – but they also make hygiene visible to the patient, who watches as the bib is disposed of after use.

Avoid bib holder contamination risk – contact the DUX Dental team today to learn more about Bib-Eze.

For more information email info@dux-dental.com or visit www.dux-dental.com.



UPDATE YOUR TEAM'S INFECTION CONTROL KNOWLEDGE

Specifically designed to meet HTM 01-05 and CQC audit requirements, Henry Schein Dental are again running their highly popular 'Infection Control & HTM 01-05' courses, in association with infection control specialists Dentisan. Recommended for the whole practice team, these seminars provide a clear understanding of the reasons why the implementation of effective cross-infection control procedures is so important.

Revised and updated for 2014 these two-hour evening sessions cover every aspect of decontamination, steering delegates through the relevant guidance and helping them create effective policies when back in practice.

Courses cost £36 and provide two hours of core verifiable CPD. Events take place throughout the UK; full details are available at www.henryschein.co.uk. Dental teams can also apply to have in-practice training delivered by infection control experts for up to 20 delegates.

For further details of locations, dates and prices, contact Sue O'Rourke on 029 2044 2818 or email suzanne.orourke@henryschein.co.uk.

SHOWCASE OFFERS EXTENDED TILL CHRISTMAS

Takara Belmont had some great deals for those attending Dental Showcase and the good news is that they'll be extending these through to the end of the year. Any customer ordering selected Belmont Treatment Centres with a unit mounted operating light will receive a free upgrade to a 900 series LED light.

Those ordering a Cleo II 'E', tbCompass 'E' or Clesta II 'E' Treatment Centre will be eligible for a free NSK 95LS (1.5 speed increasing) contra-angle. The tbCompass Treatment Centre will also be eligible for a Free NSK Varios 170 scaler. If you want to see the handpieces in action, just pop along to one of their showrooms.

Finally, those who prefer the Voyager II-L 'Surgery System' will receive a free upgrade to the 720SLR operating light (with sensor). You'll also receive a free NSK Varios 170 (basic) non-optic scaler.

Chances are technology has progressed quite a bit since your last purchase so go and see how developments could benefit you and your dental practice. Even if you're not planning to upgrade just yet, it's good to keep abreast of the latest innovation.

www.belmontdental.co.uk

QUIETER, SMALLER, LIGHTER, BETTER

Durr Dental, who pioneered suction units back in the 1960s, continues to advance technology in this area. Their new Tyscor suction machines use radial compressors instead of side channel blowers, which have a dramatic impact on energy efficiency. Typically, users save between 35%-50% in energy costs compared with traditional devices. This is because the new suction units are networkable and can be used with Tyscor Pulse software allowing the user to conveniently set their suction machine to one of three different suction levels (Eco, Balanced and Boost) all from the convenience of a PC.

The new units are also highly intuitive: an integrated rotational speed monitor detects contamination or flooding of the separation unit and, if necessary,

switches off the machine before a defect can occur.

They're also very flexible. Thanks to their modular design the Tyscor V dry systems can be quickly and easily converted to Tyscor V wet systems, offering maximum flexibility and investment protection.

Their compact size makes them easy for engineers to install, and as they're also much quieter than earlier models, they blend effortlessly into the background.

Find out more at www.durrdental.de.

